

• 520 Furnace Dock Road, Cortlandt Manor, NY 10567 • V:800.227.6784 • F:914.788.8866 • www.motionlabs.com •

# Product Specifications: Portable Chain Hoist Control Systems 8 Channel

### **Functional Specifications**

Motion Laboratories Portable 8 Channel 3Ø Chain Hoist Control Systems shall be designed to operate up to 8 serially manufactured electric chain hoists. The units shall be part of the 1200-8 series.

#### **Features**

- The unit shall have phase monitoring, where applicable.
- The unit shall have power indicators for all phases.
- The unit shall have high visibility ergonomic-grip yellow handheld remote station that features:
  - Quantity 8, 3-position directional switches.
  - Triangular UP/DOWN LED indicators.
  - Illuminated momentary GO switch.
  - Illuminated maintained KILL switch.
  - A 10 foot integrated remote cable.
  - Protective removable Lexan cover.
- The unit shall have an IEC-rated phase reversing contactor assembly.
- The unit shall have a Contactor Enable button to allow for local control at each hoist when using control pendants (pickles).
- The unit shall have PCB mount electro-mechanical control relays.
- The unit shall have Branch-rated Square D QOU-Series circuit breakers.
- The unit shall have a flexible form factor: 1 or 2 sided Motion Laboratories ATA Flight Case.
- The unit shall have a linear power supply.
- The unit shall have a modular panel design.
- The unit shall be compatible with any manufacturer's hoist.
- The unit shall be compatible with Motion Laboratories automation systems, load monitoring systems and safety systems.
- The unit shall be manufactured in the USA.

### **Physical Specifications**

All modular panels shall have a 19 inch rack width. All panels shall be made of 1/8 inch thick 5052 aluminum with a 1 inch flange and a black anodized finish. The unit shall be built into a 1 or 2 lid NEMA 1 Steel Liner, made from 14 gauge 1020 steel, with a protective Zinc chromate finish or a black satin fine texture powder coat finish.

The unit shall be labeled with the following information, using diamond scratch etching, laser etching, and/or molecularly-bonded thermal ink:`

- Motion Laboratories name/trademark.
- Electrical and environmental ratings.
- Power/Control wiring designation (Pinout).
- All necessary safety information.
- Optional customer logo.





• 520 Furnace Dock Road, Cortlandt Manor, NY 10567 • V:800.227.6784 • F:914.788.8866 • www.motionlabs.com •

## **Electrical Specifications**

The unit shall be designed to operate within the current and voltage rating of the input connector. The unit shall have variable input/output connectors, based on specific part number (see individual product sheet for details).

### **Environmental Specifications**

The unit shall be NEMA 1 Rated, for indoor use only.

### **Ratings and Certifications**

Motion Laboratories' Portable 8 Channel Chain Hoist Control System shall be a listed product as defined by the Occupational Safety and Hazard Association (OSHA). The unit shall have a **CETLus** mark and be designed and built to the following standards: UL1640, UL508A and C22.2 NO. 14 (Canadian Electric Code).